

AO-L-532 /1~600μJ/1~3W




**LD PUMPED ALL-SOLID-STATE  
AOM Q-SWITCHED LASER**

All solid state AOM Q-switched laser at 532 nm has the features of high peak power, high repetition rate, and short pulse duration, which is used in laser inner carver, laser marking, scientific research and so on.




SPECIFICATIONS

Wavelength (nm)	532±1
Operating mode	Acousto-Optic Q-switched
Average power (W)	1~3W (1W@2kHz; 3W@5kHz) Average power (W) = Single pulse energy (mJ) * Rep. rate (kHz)
Single pulse energy (μJ)	1~600 (500μJ @2kHz; 600μJ @5kHz)
Rep. rate (kHz)	0.001-10 (0.001-5k, used in laser inner carver)
Pulse duration (ns)	Typically 5~7 @<5kHz, varies from power and repetition.
Peak power (kW)	1~100 (100kW@2kHz; 100kW @5kHz)
Ave power stability (over 4 hours)	<5% , <3% , <2% , <1%
Beam divergence, full angle (mrad)	~4.5
Beam diameter at the aperture (1/e <sup>2</sup> , mm)	~1.0
Polarization ratio	>100:1, Vertical
Beam height from base plate (mm)	84.5
Warm-up time (minutes)	<10
Cooled method	Air cooled
Operating temperature (°C)	10~35
Power supply (220/110VAC)	PSU-AOM




AO-L-532



322 (L) × 145(W) × 111 (H) mm<sup>3</sup>, 5.86 kg

PSU-AOM



388 (L) × 311 (W) × 135 (H) mm<sup>3</sup>, 9.6 kg