

## 长春新产业光电技术有限公司

Changchun New Industries Optoelectronics Tech, Co., Ltd,

DATA SHEET

DPS-1064-G/50~300mJ

## HIGH ENERGY DIODE PUMPED ALL-SOLID-STATE Q-SWITCHED LASER

High energy diode pumped all solid state Q-switched laser at 1064nm has the features of high single pulse energy, high repetition rate, short pulse duration, and high peak power, which is widely used in ladar, pumped dye laser, material impact strengthening, scientific research, and so on.



## SPECIFICATIONS

1064±1		
Q-switched: EO (Electro-optic)		
100	200	300
<12		
100		
<2%, <3%		
<3		
~7.5		
<15		
108		
Water Cooled		
15~35		
PSU-DPS-G		
109		
1 year		
	Q-switched: EO (Electro-o 100 <12 100 <2%, <3% <3 ~7.5 <15 108 Water Cooled 15~35 PSU-DPS-G 10 <sup>9</sup>	Q-switched: EO (Electro-optic)   100 200   <12





