



DPS-213-Pico/1~30mW

HIGH ENERGY DIODE PUMPED ALL-SOLID-STATE Q-SWITCHED LASER

High energy diode pumped all solid state Q-switched laser at 213nm has the features of short pulse duration, high repetition rate and high average power, which is widely used in scientific research, fluorescence lifetime measurement and so on.



SPECIFICATIONS

Wavelength (nm)	213±1	
Operating mode	Pulsed	
Output power (mW)	10	30
Power stability (rms, over 4 hours)	<3%, <1%	
Pulse width (ps)	<50	
Beam divergence, full angle (mrad)	<3	
Beam diameter (mm)	~2	
Repetition frequency (MHz)	5	
Beam height from base plate (mm)	128	
Cooled method	Air cooled	
Warm-up time (minutes)	<15	
Operating temperature (°C)	15~30	
Power supply (AC 220V)	PSU-DPS-Pico	
Expected lifetime (hours)	10000	
Warranty	1 year	

