


DPS-280-R/1~500μJ

**HIGH ENERGY DIODE
PUMPED ALL-SOLID-STATE
Q-SWITCHED LASER**

High energy diode pumped all solid state Q-switched laser at 280nm has the features of high single pulse energy, short pulse duration, and high peak power, which is widely used in Lidar, Laser spectroscopy, Sensing and metrology, and so on.



SPECIFICATIONS

Wavelength (nm)	280±1
Operating mode	Q-switched: EOM (Electro-optic modulation)
Single pulse energy (uJ)	≤500
Pulse duration (ns)	≤10
Rep. rate (Hz)	1~100 (adjustable)
Energy stability	<5%
Beam divergence, full angle (mrad)	<25
Beam diameter (mm)	~2×2
Warm-up time (minutes)	<15
Cooled method	Air Cooled or Water Cooled
Operating temperature (°C)	15~30
Power supply	DC 48V
Expected lifetime(pulses)	10 ⁹
Warranty period	1 year