



FC-W-976H/50~500W


**HIGH POWER FIBER COUPLING
DIODE LASER SYSTEM AT 976 nm**

The FC-W-976H series (Fiber Coupling Laser System) have integrated laser diode, fiber coupling optics, laser power supply, LD current and temperature control in ONE box. Its compact dimension and convenient functions, such as power adjustment, temperature control, LED display etc, make it very suitable for pumping, scientific research, industrial and medical applications.




SPECIFICATIONS

Model	FC-W-976H	
Wavelength (nm)	976±10	
Operating mode	CW	
After fiber output power (W)	>50, 60, ... , 200	200~500(On request)
Power stability (rms, over 4 hours)	<2%, <1%, <0.5%	
Red pilot light	Available on request	
Fiber core diameter (µm)	400	
Fiber NA	0.22	
Fiber connector	SMA905	
Fiber length (m)	2	
LED display	Diode current	
Operating temperature (°C)	10~40	
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional	
Input power	100-240VAC, 50 to 60 Hz	
Cooling Way	Air Cooled	Water Cooled
Dimensions(mm ³)	425 (L) × 373 (W) × 148 (H)	On request
Expected lifetime (hours)	10000	
Warranty	1 year	



FC-W-976H



425 (L) × 373 (W) × 148 (H) mm³, 14.4 kg