

## Laser Power Meter



HP50

### Features:

1. Wavelength range: 0.19-25  $\mu\text{m}$
2. Power range: 0.5W - 50W
3. Active area diameter: 22mm

### SPECIFICATIONS

Handheld Power Meter	HP50
Power Range	0.5W - 50W
Active area diameter	22mm
Wavelength range	0.19-25 $\mu\text{m}$
Max. Power Density	40 kW/cm <sup>2</sup>
Uncertainty(k=2)	$\pm 2\%$
Linearity	$\pm 1\%$
Battery model	BL-5C
Cooling method	Air cooling
Operating temperature	5°C-45°C(41°F-113°F)
Storage temperature	-20°C-70°C (-4°F-158°F)
Warranty period	1 year

Handheld Power Meter HP50

