


## ■ Features




- ◆ High output power of 30W
- ◆ 400μm/0.22NA multimode optical fiber
- ◆ Center wavelength 638±10nm

## ■ Applications

- ◆ Scientific Research
- ◆ Lighting
- ◆ Medical Application



## Outline Dimension (mm)



Pin-out Assignment

Pin	Function	Pin	Function
1	LD1(+)	13	PD(N)
2	LD1(-)	14	PD(P)
3	LD2(+)		
4	LD2(-)		
5	LD3(+)		
6	LD3(-)		
7	LD4(+)		
8	LD4(-)		
9	Thermistor		
10	Thermistor		
11	Indicating light (+2.7v)		
12	Indicating light (0v)		

## Typical Device Performance (20°C)

	Min	Typical	Max	Unit
<b>Optical</b>				
CW Output Power	-	30	-	W
Center Wavelength	-	638±10	-	nm
Spectral Width (90% of Power)	-	4.0	-	nm
<b>Electrical*</b>				
Threshold Current	-	-	0.17	A
Operating Current (Simplex)	-	2.2	2.2	A
Operating Voltage (Simplex)	-	18	-	V
<b>Indicating light</b>				
Output Power	-	<3	-	mW
Center Wavelength	-	637±10	-	nm
Operating Current	-	<50	-	mA
Operating Voltage	-	2.7	-	V
<b>Fiber*</b>				
Fiber Core Diameter	-	400	-	μm
Numerical Aperture	-	0.22	-	-
Fiber Length	-	1-5	-	m
Fiber Connector	-	FC/SMA905	-	-
Fiber Armor	-	Optional	-	-
Fiber Minimum Bending Diameter	75	-	-	mm

The power supply mode of the laser has four power supplies.

## Absolute Rating

	Min	Max	Unit
Operating Temperature	15	35	°C
Operating Relative Humidity	-	75	%
Storage Temperature	-20	80	°C
Storage Relative Humidity	-	90	%
Lead Soldering Temperature (10 s max)	-	250	°C

\* Measuring specifications.

All figures in this specification are measured by CNI's method and may contain measurement deviations.

The above specifications are for reference purpose only and subjected to change without prior notice.

