

LPS-2940-S/100~200mJ


SPECIFICATIONS




**HIGH ENERGY LAMP PUMPED PULSED LASER**

High energy lamp pumped pulsed laser at 2940nm has the features of high single pulse energy, the wavelength and water absorption peaks is overlap ,which is widely used in ranging, medical treatment, scientific research, laser cosmetology, optical sensor and other applications, and so on.



Wavelength (nm)	2940±1	
Operating mode	Pulsed	
Single pulse energy (mJ)	100	200
Pulse duration (ms)	0.9	
Rep. rate (Hz)	2~5	
Energy stability	<5%, <3%, <2%	
Beam diameter (mm)	5	
Warm-up time (minutes)	<15	
Beam height from base plate (mm)	75	
Cooled method	Water Cooled	
Operating temperature (°C)	15~35	
Power supply (220V AC)	PSU-LPS-S	
Expected lifetime (pulses)	10 <sup>7</sup>	
Warranty period	1 year	



LPS-2940-S	PSU-LPS-S	Water Chiller
 <p>381(L) × 150(W) × 130(H) mm<sup>3</sup>, 9.4kg</p>	 <p>480 (L) × 500(W) × 275(H) mm<sup>3</sup>, 25kg</p>	 <p>580(L) × 290(W) × 470(H) mm<sup>3</sup>, 24 kg</p>