

MDL-F-470/1000~2000mW



**BLUE DIODE LASER
AT 470nm**

Diode laser module at 470nm features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in scientific research, ect.



SPECIFICATIONS

Central wavelength (nm)	470±10
Operating mode	CW
Output power (mW)	>1000, 1100, 1200, ...,2000
Power stability (rms, over 4 hours)	<1%, <2%, <3% (<0.5%, optional)
Transverse mode	Multimode
Beam diameter at the aperture ((1/e ² ,mm)	~2.7×2.7
Beam divergence, full angle (mrad)	1.4×0.2
Polarization ratio	>50:1 (>100:1, optional) Horizontal±5 degree (Vertical Optional)
Warm-up time (minutes)	<5
Beam height from base plate (mm)	45
Operating temperature (°C)	10~35
Power supply (100-240VAC)	PSU-H-LED/ PSU-H-FDA
TTL / Analog modulation	TTL or Analog with 1Hz-1KHz 1KHz-10KHz, 10KHz-30KHz optional
Expected lifetime (hours)	10000
Warranty	1 year



MDL-F-470	PSU-H-LED	PSU-H-FDA
<p>216.5 (L) ×88(W) ×74 (H) mm³, 1.4kg</p>	<p>277 (L) ×145(W) ×106(H) mm³, 2.3kg</p>	<p>275 (L) ×145(W) ×104(H) mm³, 2.1kg</p>