



MDL-H-1720/1~1000mW




**INFRARED DIODE LASER
AT 1720nm**

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are used in measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	1720±5	
Operating mode	CW	
Output power (mW)	>1, 100, 200, ... , 1000	
Power stability (rms, over 4 hours)	<3%, <2%, <1%	
Transverse mode	Multimode	
Dimensions of beam at the aperture (mm)	~5×8	
Beam divergence, full angle (mrad)	<3.0	
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	29	
Operating temperature (°C)	10~35	
Power supply (100-240VAC)	PSU-H-LED	PSU-H-FDA
Modulation optional	TTL on/off, 1Hz-1kHz, 1kHz-10kHz, 10kHz-30kHz; and Analog modulation optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



MDL-H-1720	PSU-H-LED	PSU-H-FDA
<p style="text-align: center;">160 (L) × 77(W) × 60 (H) mm³, 0.9kg</p>	<p style="text-align: center;">277 (L) × 145(W) × 106(H) mm³, 2.3kg</p>	<p style="text-align: center;">275 (L) × 145(W) × 104(H) mm³, 2.1kg</p>