



MDL-SD-445/447/450-OEM/3500-4000mW




**OEM BLUE DIODE LASER
AT 445/447/450nm**

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in scientific research, laser pointing, show and RGB mixed laser systems applications.



SPECIFICATIONS

Central wavelength (nm)	445±5/ 447±5/ 450±5	
Operating mode	CW	
Output power (mW)	>3500, 3600,...,4000	
Power stability (rms, over 4 hours) at 25°C	<1%, <2%, <3%	
Polarization direction	Horizontal/ Vertical	Horizontal+ Vertical
Beam diameter at the aperture (mm)	~4.7×2.7	~2.7×2.7
Beam divergence, full angle (mrad)	~1.4×0.2	
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	28.5	
Operating temperature (°C)	25+/-3	
Driver (12VDC 15A)	PSU-SD-OEM	
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



MDL-SD-445/447/450-OEM	PSU-SD-OEM	Accessory (Power supply 100-240VAC)
<p>107(L)×77(W)×51(H) mm³, 1.0kg</p>	<p>90.5 (L)×47(W)×56(H) mm³, 0.3kg</p>	<p>177.5(L)×62(W)×30(H) mm³, 0.5 kg</p>