DATA SHEET

MIL-W-2128/1~1500mW

## LD PUMPED ALL-SOLID-STATE INFRARED LASER AT 2128nm

All solid state 2128nm infrared laser is made features of high power ,good beam quality and easy operating, which is widely used in material processing especially for plastics, it use for pumping of laser sources for the mid infrared region, medical procedures such as precise tissue ablation, ophthalmic surgery or dentistry, suppresses the bleeding during operations, etc.









## SPECIFICATIONS

Wavelength (nm)	2128±5
Operating mode	CW
Output power (mW)	>1, 100, 200,1500
Power stability (rms, over 4 hours)	<2%, <3%, <5%
Beam divergence, full angle (mrad)	<6
Beam diameter at the aperture (1/e²,mm)	<4
Beam height from base plate (mm)	108.5
Warm-up time (minutes)	<10
Operating temperature (°C)	15~30
Power supply (90-264VAC)	PSU-W-FDA or PSU-W-LED
Expected lifetime (hours)	10000
Warranty period	1 year
·	





