

# MK-1064 Laser Marking System

High Power Laser Marking System For Family And Factory




Features:	Material:
<ul style="list-style-type: none"> <li>- Best price / performance ratio</li> <li>- Easy assembly, simple structure</li> <li>- Small volume, portable and mobile</li> <li>- Air cooled with ultra-compact design</li> </ul>	<ul style="list-style-type: none"> <li>- Metal (gold, silver, copper, Iron, aluminum, titanium, zinc, steel...)</li> <li>- Plastic (PC、PVC、PE、HDPE、ABS、PPR、PET、HIPS、PS、PP、PPO、PA、POM、PMMA...)</li> <li>- Others (Oil paint surface, coating surface, plastic film, package...)</li> </ul>

## Specifications

Type	MK-1064
Wavelength	1064nm
Peak power	>30kW
Pulse width	~5ns
Marking scope	110 x 110mm
Marking depth	<1mm
Maximum marking line speed	7000mm/s
Minimum marking line width	0.03mm
Power consumption	~100W
Power requirement	90-240VAC/ 50~60Hz
Weight	~6KG
Size	345X130X167mm

## Dimensions



## Marking Samples


Jewelry (gold, silver)



Kitchen&bath (stainless steel)



Scaleplate (copper, Iron, aluminum)



Metal shell (black aluminum, steel)



Plastic (PC、PVC、PE、HDPE、ABS、PPR、PET、HIPS、PS、PP、PPO、PA、POM)




## Components (optional)


L-type Fixture



U-type Fixture



Rotary fixture



Laser Goggles



Metal Card



Lead screw

