




MLL-U-xxx-SU series



LOW NOISE INFRARED LASER

All solid state low noise infrared laser is made features of ultra compact, long lifetime, low cost and easy operating, which is used in scientific experiment, optical sensor, measurement, instrument, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	914±1		946±1		1047±1		1053±1		1064±1
Operating mode	CW								
Output power (mW)	1-200	200-400	1-150	150-300	1-800	800-1000	1-500	500-1500	1500-3000
Power stability (rms, over 4 hours)	<3%, <2%, <1%	<3%, <2%	<3%, <2%, <1%	<3%, <2%	<3%, <2%		<3%, <2%, <1%	<3%, <2%	<3%, <2%, <1%
Transverse mode	TEM ₀₀								
Spectral line width (nm)	<1.0, <0.1, <0.006	<1.0, <0.1	<1.0, <0.1, <0.006	<1.0, <0.1	<1.0, <0.1, <0.006	<1.0, <0.1	<1.0, <0.1, <0.006	<1.0, <0.1	
Noise of amplitude (rms, 1Hz~20MHz)	<1%								
M ² factor	<1.2			<1.5					
Beam diameter at the aperture (1/e ² , mm)	~1.5								
Beam divergence, full angle (mrad)	<1.5								
Polarization Ratio	>100:1, Horizontal (Vertical Optional)		/		>100:1, Horizontal (Vertical Optional)				
Warm-up time (minutes)	<5								
Pointing stability after warm-up (mrad)	<0.05								
Beam height from base plate (mm)	27.4								
Operating Temperature (°C)	10~35								
Power supply (90-264VAC)	PSU-H-FDA/PSU-H-OEM								
Expected lifetime (hours)	10000								
Warranty	1 year								

Note: The laser head needs to be used on a heat sink with good heat dissipation.



SPECIFICATIONS

Central wavelength (nm)	1085±2		1112±3		1122±3		1313±1	
Operating mode	CW							
Output power (mW)	1-500	500-1000	1-50	50-100	1-200	200-300	1-700	700-1000
Power stability (rms, over 4 hours)	<3%, <2%, <1%,	<3%, <2%	<3%, <2%, <1%,	<3%, <2%	<3%, <2%, <1%,	<3%, <2%	<3%, <2%, <1%,	<3%, <2%
Transverse mode	TEM ₀₀							
Spectral line width (nm)	<1.0, <0.1, <0.006	<1.0, <0.1	<1.0, <0.1, <0.006	<1.0, <0.1	<1.0, <0.1, <0.006	<1.0, <0.1	<1.0, <0.2, <0.006	<1.0, <0.1
Noise of amplitude (rms, 1Hz~20MHz)	<1%							
M ² factor	<1.5						<1.2	
Beam diameter at the aperture (1/e ² , mm)	~1.5							
Beam divergence, full angle (mrad)	<1.5							
Polarization Ratio	>100:1, Horizontal (Vertical Optional)			/			>100:1, Horizontal (Vertical Optional)	
Warm-up time (minutes)	<5							
Pointing stability after warm-up (mrad)	<0.05							
Beam height from base plate (mm)	27.4							
Operating Temperature (°C)	10~35							
Power supply (90-264VAC)	PSU-H-FDA/PSU-H-OEM							
Expected lifetime (hours)	10000							
Warranty	1 year							

Note: The laser head needs to be used on a heat sink with good heat dissipation.






SPECIFICATIONS

Central wavelength (nm)	1319±1		1342±1		1444±2
Operating mode	CW				
Output power (mW)	1-200	200-500	1-800	800-2000	1-400
Power stability (rms, over 4 hours)	<3%, <2%, <1%,	<3%, <2%	<3%, <2%, <1%,	<3%, <2%	<3%, <2%
Transverse mode	TEM ₀₀				
Spectral line width (nm)	<1.0, <0.2, <0.006	<1.0, <0.1	<1.0, <0.2, <0.006	<1.0, <0.1	<1.0, <0.1
Noise of amplitude (rms, 1Hz-20MHz)	<1%				
M ² factor	<1.5		<1.2		<1.5
Beam diameter at the aperture (1/e ² , mm)	~1.5				
Beam divergence, full angle (mrad)	<1.5				
Polarization Ratio	>100:1, Horizontal (Vertical Optional)				
Warm-up time (minutes)	<5				
Pointing stability after warm-up (mrad)	<0.05				
Beam height from base plate (mm)	27.4				
Operating Temperature (°C)	10~35				
Power supply (90-264VAC)	PSU-H-FDA/PSU-H-OEM				
Expected lifetime (hours)	10000				
Warranty	1 year				

Note: The laser head needs to be used on a heat sink with good heat dissipation.



LASER HEAD	POWER SUPPLY (PSU-H-FDA)	POWER SUPPLY (PSU-H-OEM)
 <p>160(L)×60(W)×50(H) mm³, 0.9kg</p>	 <p>276.6(L)×145(W)×103.6(H) mm³, 2.3 kg</p>	 <p>235(L)×110(W)×45(H) mm³, 1.1kg</p>