

长春新产业光电技术有限公司

Changchun New Industries Optoelectronics Tech. Co., Ltd.

DATA SHEET

OEM-W-532/10~18W



LD PUMPED ALL-SOLID-STATE GREEN LASER

All solid state 532nm green laser is made features of ultra compact, long lifetime and easy operating, which is widely used in collimation, laser medical treatment, scientific experiment, optical instrument, laser display, laser lighting show, etc.









SPECIFICATIONS

Wavelength (nm)	532±1
Model	OEM-W
Operating mode	CW
Output power (W)	10, 11,,18
Power stability (rms, over 4 hours)	<1%, <2%, <3%, <5%
Transverse mode	Near TEM ₀₀
M ² factor	3.0~6.0
Beam divergence, full angle (mrad)	<1.5
Beam diameter at the aperture (1/e², mm)	~4.0
Polarization ratio	>100:1
Warm-up time (minutes)	<10
Beam height from base plate (mm)	30
Operating temperature (°C)	22.5+/-2.5
Driver (12VDC 25A)	PSU-OEM-W
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty time	1 year





Note: The laser needs to be used on a heat sink with good heat dissipation.

#