



SF-III-1550/1~10mW



**INFRARED DIODE LASER
AT 1550nm**

It features ultra a narrow linewidth, compact design, long lifetime, cost-effectiveness and easy operation. They are used in communication, tracking, telemetry and antenna remoting, etc.



SPECIFICATIONS

Central wavelength (nm)	1550±3	
Spectral linewidth (nm)	~0.6	
Operating mode	CW	
Output power (mW)	>1, 2, 3, ..., 10	
Power stability (rms, over 4 hours)	<1%, <2%, <3%	
Transverse mode	Near TEM ₀₀	
Dimensions of beam at the aperture (1/e ² ,mm)	~1.0	
Beam divergence, full angle (mrad)	<2.5	
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	24.8	
Operating temperature (°C)	10~35	
Power supply	85-264VAC	PSU-III-LED/ PSU-III-FDA (Frequency for 1Hz-30kHz)
	100-240VAC	PSU-A-D (Frequency for 30kHz -100kHz)
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz, 30kHz-100kHz optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



SF-III-1550	PSU-III-LED	PSU-III-FDA	PSU-A-D
<p>143.5(L)×73(W)×46.2(H) mm³, 0.7kg</p>	<p>188.6(L)×155(W)×92(H) mm³, 1.5kg</p>	<p>171(L)×130(W)×62.2(H) mm³, 1.2kg</p>	<p>162(L)×144(W)×70(H) mm³, 1.0kg</p>