

TEM-F-1392DFB/1~10mW (TEM₀₀)




INFRARED DIODE LASER AT 1392nm

It features TEM₀₀ mode, ultra compact design, long lifetime, cost-effectiveness and easy operation. They are used in measurement, communication, spectrum analysis, etc



SPECIFICATIONS

Central wavelength (nm)	1392±2	
Operating mode	CW	
Output power (mW)	>1,2,3.....,10	
Power stability (rms, over 4 hours)	<3%, <2%, <1%, <0.5%	
Transverse mode	TEM ₀₀	
Ellipticity	>0.95	
M ² factor	<1.1	
Spectral linewidth (MHz)	~3	
Beam diameter at the aperture (1/e ² ,mm)	~1.0	
Beam divergence, full angle (mrad)	<1.5	
SMSR (dB)	35	
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	25	
Operating temperature (°C)	25±/-3	
Power supply (85-264VAC)	PSU-III-LED	PSU-III-FDA
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



Note: The laser head needs to be used on a heat sink with good heat dissipation.

TEM-F-1392DFB	PSU-III-LED	PSU-III-FDA
<p style="text-align: center;">146 (L) × 58(W) × 45 (H) mm³, 0.7kg</p>	<p style="text-align: center;">188.6 (L) × 155(W) × 92 (H) mm³, 1.5kg</p>	<p style="text-align: center;">171(L) × 130(W) × 62.2 (H) mm³, 1.2kg</p>