

YL-I-520 1~10W

DIODE LASER AT 520nm

Diode laser 520nm is made features of ultra compact, long lifetime, low cost and easy operating. It's easy to be installed in customer's equipment.




SPECIFICATIONS


Wavelength (nm)	520±5
Operating mode	CW
Output power (W) @ after 400um fiber	1~10
Fiber Core Diameter (um)	100, 200, 400, 600
Fiber Connector	SMA905/ FC
Numerical Aperture (NA)	0.22
Fiber length (m)	1 (Fiber length can be customized)
Power stability (rms, over 4 hours)	<1%
Cooled method	With TEC/ without TEC optional
Warm-up time (minutes)	<5
Operating temperature (°C)	25+/-3
Expected lifetime (hours)	10000
Warranty	1 year



Dimensions of Laser head (Without TEC)




Dimensions of Laser head (With TEC)




1-4W

103.6 (L)*55 (W)*32 (H) mm³



5-7W

113.5 (L)*68 (W)*32 (H) mm³



8-10W

142.5 (L)*68 (W)*32 (H) mm³