

DATA SHEET

AO-Z-473 /1~50uJ/1~500mW

LD PUMPED ALL-SOLID-STATE **AOM Q-SWITCHED LASER**

All solid state AOM Q-switched laser at 473 nm has the features of high peak power, high repetition rate, and short pulse duration, which is widely used in marking, carving, measure, research and so on.





SPECIFICATIONS

Wavelength (nm)	473±1
Operating mode	Q-switch: AOM (Acousto-Optic Modulation)
Output power(mW)	1~500
Single pulse energy (µJ)	1~50
Pulse duration (ns)	~230@10kHz
Peak power (W)	~210
Rep. rate (kHz)	1~50, adjustable by external control
Ave power stability (over 4 hours)	<5%, <10%
Warm-up time (minutes)	<10
Beam divergence, full angle (mrad)	<2
Beam diameter at the aperture (mm)	~4.0
Beam height from base plate (mm)	96
Cooled method	Air cooled
Operating temperature (°C)	10~35
Power supply (220/110VAC)	PSU-AOM(3U)
Expected lifetime (hours)	10000
Warranty period	1 year





AO-Z-473 **Dimensions** PSU-AOM(3U) **Dimensions** 4-6*7 485(L) ×381(W) ×133 (H) mm3, 12.4kg 440(L)×114(W) ×130(H) mm³, 9.8 kg