



DPS-355-Pico/100~700mW


**HIGH ENERGY DIODE
PUMPED ALL-SOLID-STATE
Q-SWITCHED LASER**

High energy diode pumped all solid state Q-switched laser at 355nm has the features of short pulse duration, high repetition rate and high average power, which is widely used in laser medical treatment, industrial processing, physics experiment, scientific research, and so on.



SPECIFICATIONS

Wavelength (nm)	355±1	
Operating mode	Pulsed	
Output power (mW)	300	700
Power stability (rms, over 4 hours)	<5%, <3%	
Pulse width (ps)	<50	
Beam divergence, full angle (mrad)	<3	
Beam diameter (mm)	~2	
Repetition frequency (MHz)	5	
Beam height from base plate (mm)	128	
Cooled method	Air cooled	
Warm-up time (minutes)	<15	
Operating temperature (°C)	15~30	
Power supply (AC 220V)	PSU-DPS-Pico	
Expected lifetime (hours)	10000	
Warranty	1 year	



DPS-355-Pico	PSU-DPS-Pico
<p style="text-align: center;">465(L)×500(W)×170(H) mm³ 65kg</p>	<p style="text-align: center;">850(L)×545(W)×590(H) mm³ 85kg</p>