



EO-S-1064/1~300μJ/1~300mW

SPECIFICATIONS

**LD PUMPED ALL-SOLID-STATE
ELECTRO-OPTIC Q-SWITCHED
LASER AT 1064 nm**

All solid state electro-optic Q-switched laser at 1064 nm has the features of high single pulse energy, short pulse duration, and high peak power, which is widely used in laser distance measuring, laser Radar, laser Raman, ICP-MS, LIBS, scientific research and so on.



Wavelength (nm)	1064±1
Operating mode	Electro-optics Q-switched
Single pulse energy (μJ)	1~300 (300μJ @ 1kHz; 250μJ @ 100Hz)
Pulse duration (ns)	~8
Rep. rate (Hz)	1~1000
Pulse Jitter (Sdev) @ 1kHz	<1ns
Average power (mW)	Average power (mW) = Single pulse energy (μJ)* Rep. rate (kHz)
Power Stability (rms, over 4 hours)	<1%, <2%, <3%, <5%
Beam Diameter at the aperture 1/e ² (mm)	~1.3
Beam divergence, full angle (mrad)	<1.5
Warm-up Time (minutes)	<10
Beam height from base plate (mm)	35
Operating temperature (°C)	10~35
Power supply (90-264VAC)	PSU-EOM-DL
Expected lifetime (hours)	10000
Warranty	1 year

*Precision of digital oscilloscope: bandwidth 1GHz; sample rate: 10GS/s.

Note: The laser head needs to be used on a heat sink with good heat dissipation.



EO-S-1064	PSU-EOM-DL
<p>227 (L) × 75 (W) × 75 (H) mm³, 2.05kg</p>	<p>270 (L) × 214 (W) × 99 (H) mm³, 3.02 kg</p>