

FC-660/808-CH



FC-660/808-CH Laser System

It can combine 2 wavelengths into a system and two fibers output. It can control the laser output either separately, or open multiple lasers at the same time.




SPECIFICATIONS

Wavelength combination (nm)	CH1: 660, CH2: 808
Wavelength (nm)	±5@660nm, ±10@808nm
Operating mode	CW
Output power after fiber	2W@660nm, 2W@808nm
Power stability (rms, over 4 hours)	<3%, <2%, <1%
Output type	Two channels output
Fiber type	MM fiber
Fiber Core Diameter(μm)	400/ 200
Fiber Connector	SMA905/ FC
Fiber Length (m)	1m (Other lengths are available on request)
Fiber jacket	PVC or metal jacket
Warm-up time (minutes)	<5
Operating temperature (°C)	10~35
Input voltage	100-240VAC
Modulation optional	TTL on/off, 1Hz-1kHz, 1kHz-10kHz, 10kHz-30kHz; and Analog modulation optional
Expected lifetime (hours)	10000
Warranty	1 year

Remark: Please consult CNI for customized configurations and modifications available.

FC-660/808-CH



330 (L)×291 (W) ×156 (H) mm³