



FL-355-Pico/1~50mW

PICOSECOND ALL FIBER PULSED LASER

Picosecond all fiber pulsed laser at 355nm is made features of high output power stability, good beam profile, ultra compact, long lifetime, cost-effectiveness and easy operating, which is widely used in scientific research, laser processing, and so on.



SPECIFICATIONS

Wavelength (nm)	355±1		
Operating mode	Pulsed		
Output power (mW)	10@5MHz	30@5MHz	50@5MHz
Power stability (rms, over 4 hours)	<3%, <5%		
Pulse width (ps) ⁽¹⁾	One fixed value between 100~900ps		
M ² factor	<1.8		
Repetition frequency (MHz) ⁽²⁾	One fixed value between 0.1~20MHz		
Polarization ratio	> 15dB		
Warm-up time (minutes)	<15		
Beam height from base plate (mm)	30		
Delivery cable length (m)	variable		
Operating temperature (°C)	15~35		
Power supply	220V AC / 12V DC		
Expected lifetime (hours)	10000		
Warranty	1 year		
Options	(1) Pulse width 100~900ps variable (2) Repetition rate 0.1~20MHz variable RS 232 interface Higher output power can be customized		



FL-1064-Pico	Third harmonic	FL-355-Pico
<p>344(L)×200(W)×100(H) mm³ 6.5kg</p>	<p>364(L)×125(W)×67(H) mm³ 1.1kg</p>	<p>Third harmonic FL-1064-Pico</p>