



GLP-650/5mW

**LASER POINTER  
AT 650nm**



GLP-650 is noticeable and the red beam itself can be seen in mid-air in dark conditions, not just a laser beam dot. In addition, it is FDA approved.



SPECIFICATIONS

Wavelength (nm)	650±10
Output power (mW)	5
Transverse mode	Near TEM <sub>00</sub>
Operating mode	CW
Beam divergence, full angle (mrad)	0.2
Beam diameter at the aperture (mm)	2
Working Voltage DC (V)	3.2
Working Temperature (°C)	0-40
Switch	Push button
Surface color	Black
Power supply	2×AAA/1.5V batteries
Operating lifetime (hours)	3000~5000
Warranty	6 months
Remark	LED indicator, key switch and logo engraving are on your request.



GLP-650	Battery	With diffraction grating
 <p>Φ13.5×140(L) mm<sup>3</sup>, 0.055 kg</p>	 <p>2×AAA/1.5V batteries</p>	