

HPL-660-Q/20~50W

SPECIFICATIONS





**WATER COOLING LD PUMPED  
ALL-SOLID-STATE Q-SWITCHED  
RED LASER at 660nm**

All solid state Q-switched red laser at 660nm has the features of high peak power, high repetition rate, and short pulse duration, which is widely used in laser measurement, laser display, scientific research, military, and so on.



Wavelength (nm)	660±1	
Operating mode	Q-switched: AOM (Acousto-Optic Modulation)	
Average power (W)	>20	>50
Pulse duration (ns)	~150 @10kHz	
Rep. rate (kHz)	10~20 (It is possible to customize other repetition rates )	
Single pulse energy (mJ)	>2 @10kHz	>5 @10kHz
Peak power (kW)	>10 @ 10kHz	>30 @10kHz
Ave power stability (over 4 hours)	<3% or <5%	
Beam divergence, full angle (mrad)	<3.5	
Beam diameter at the aperture (mm)	≥9	≥12
Beam height from base plate (mm)	55	
Warm-up time (minutes)	<10	
Cooled method	Water Cooled	
Operating temperature (°C)	15~35	
Power supply (220/110VAC)	PSU-HPL(2U×2)	
Expected lifetime (hours)	10000	
Warranty period	1 year	



HPL-660-Q(20~50W)	PSU-HPL-Q(2U)	PSU-HPL-CW(2U)	Water Chiller
 <p>445 (L) ×238(W) ×124(H) mm<sup>3</sup>, 15kg</p>	 <p>380(L) ×485(W) ×90(H) mm<sup>3</sup>, 7.5kg</p>	 <p>288(L) ×482(W) ×90(H) mm<sup>3</sup>, 5.5kg</p>	 <p>475 (L) ×575(W) ×805(H) mm<sup>3</sup>, 71kg(20W) 505 (L) ×625(W) ×905(H) mm<sup>3</sup>, 95kg(50W)</p>