

450nm Laser Diode

■ Features



- ◆ High output power of 10W
- ◆ 200μm/0.22NA multimode optical fiber
- ◆ Center wavelength 450±10nm

■ Applications


- ◆ Medical Application
- ◆ Scientific Research



Outline Dimension (mm)



Pin-out Assignment	
Pin	Function
1	Fiber Connector Detector LED (+)
2	Fiber Connector Detector LED (-)
3	-
4	-
5	-
6	Thermistor
7	Thermistor
8	-



Typical Device Performance (25°C)

	Min	Typical	Max	Unit
Optical				
CW Output Power	-	10	-	W
Center Wavelength	-	450±10	-	nm
Electrical				
Threshold Current	-	0.32	-	A
Operating Current	-	2.3	-	A
Operating Voltage	-	16.7	-	V
Slope Efficiency	-	5	-	W / A
Power Conversion Efficiency	-	26	-	%
Fiber*				
Fiber Core Diameter	-	200	-	μm
Fiber Cladding Diameter	-	220	-	μm
Fiber Length	-	1~5	-	m
Fiber Connector	-	-	-	-

* Customized fiber and connector available.


Absolute Ratings

	Min	Max	Unit
Operating Temperature	15	35	°C
Operating Relative Humidity	-	75	%
Cooling Mode	-	Water cooling (25°C)	-
Storage Temperature	-20	80	°C
Storage Relative Humidity	-	90	%
Lead Soldering Temperature (10 s max)	-	250	°C

* Measuring specifications.

All figures in this specification are measured by CNI's method and may contain measurement deviations.

The above specifications are for reference purpose only and subjected to change without prior notice.



Changchun New Industries Optoelectronics Tech. Co., Ltd
<http://www.cnilaser.com>

◆ CONTACT

No.668, Chuangxin Road, High-tech zone,
 Changchun 130012, China

Phone: 0086-431-85603799

Fax: 0086-431-87020258