



LDM-450-120

Typical Device Performance (25°C)

Optical	Unit	Typical Value
CW Output Power	W	120
Center Wavelength	nm	450±10
Electrical		
Threshold Current	A	0.2
Operating Current	A	1.5
Operating Voltage	V	50
Power supply		8 channels
Fiber		
Fiber Core Diameter	μm	800
Fiber Cladding Diameter	μm	880
Fiber Buffer Diameter	μm	1030
Numerical Aperture	-	0.22
Fiber Length	m	1~5

*8 groups of LD assembled inside the module, 1.5A current and 50v voltage operating of each group.


Absolute Ratings

	Unit	Min	Max
Operating Temperature	°C	10	40
Operating Relative Humidity	%	-	75
Storage Temperature	°C	-20	80
Storage Relative Humidity	%	-	90
Lead Soldering Temperature, 10 s max	°C	-	250

Addr: No.888 Jinhua Road High-tech Zone, Changchun 130103, P.R.China

Contact: sales@cnilaser.com International Tel: +86-431-85603799 Fax: +86-431-87020258

Package Dimensions (mm)



Addr: No.888 Jinhua Road High-tech Zone, Changchun 130103, P.R.China

Contact: sales@cnilaser.com International Tel: +86-431-85603799 Fax: +86-431-87020258