



LDM-520-30

Typical Device Performance (25°C)

Optical	Unit	Typical Value
CW Output Power	W	30
Center Wavelength	nm	520, ± 10
Electrical		
Threshold Current	A	0.3
Operating Current	A	1.8
Operating Voltage	V	60
Power supply mode*		3 channels
Fiber		
Fiber Core Diameter	μm	400
Fiber Cladding Diameter	μm	440
Fiber Buffer Diameter	μm	700
Numerical Aperture	-	0.22
Fiber Length	m	1~5

*3 groups of LD assembled inside the module, 1.8A current and 60v voltage operating of each group.

Absolute Ratings

	Unit	Min	Max
Operating Temperature	°C	10	40
Operating Relative Humidity	%	-	75
Storage Temperature	°C	-20	80
Storage Relative Humidity	%	-	90
Lead Soldering Temperature, 10 s max	°C	-	250

Package Dimensions (mm)

