



LDM-808-7

Typical Device Performance (25°C)

Optical	Unit	Typical Value
CW Output Power	W	7
Center Wavelength	nm	808±3
Spectral Width (90% of Power)	nm	<0.5
Wavelength Shift with Temperature	nm / °C	0.3
Wavelength Shift with Current	nm / A	1
Feedback Protection (1030-1100nm)	dB	>40
Electrical		
Threshold Current	A	0.9
Operating Current	A	7.5
Operating Voltage	V	1.9
Slope Efficiency	W / A	1.1
Power Conversion Efficiency	%	49
Fiber		
Fiber Core Diameter	μm	105
Fiber Cladding Diameter	μm	125
Fiber Buffer Diameter	μm	250
Numerical Aperture	-	0.22
Fiber Length	m	1.0


Absolute Ratings

	Unit	Min	Max
Operating Temperature	°C	10	40
Operating Relative Humidity	%	-	75
Storage Temperature	°C	-20	80
Storage Relative Humidity	%	-	90
Lead Soldering Temperature, 10 s max	°C	-	250


Addr: No.888 Jinhu Road High-tech Zone, Changchun 130103, P.R.China

Contact: sales@cnlaser.com International Tel: +86-431-85603799 Fax: +86-431-87020258

Characteristics of 808nm-7W laser diode module (25°C)






Typical spectrum of 808nm-7W laser diode module (25°C)



Addr: No.888 Jinhua Road High-tech Zone, Changchun 130103, P.R.China

Contact: sales@cnlaser.com International Tel: +86-431-85603799 Fax: +86-431-87020258

Package Dimensions (mm)



Pin Assignment	
Pin	Function
1	Laser (+)
2	Laser (-)



Addr: No.888 Jinhua Road High-tech Zone, Changchun 130103, P.R.China

Contact: sales@cnilaser.com International Tel: +86-431-85603799 Fax: +86-431-87020258