



MBL-U-457 /1-400mW




**HIGH STABILITY DPSS LASER
AT 457nm**

High stability DPSS laser at 457nm is made features of ultra compact, long lifetime, high stability and reliability, which is used in scientific experiment, medical measurement, instrument, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	457±1	
Operating mode	CW	
Output power (mW)	>1, 5, 10, 20, ..., 150	>150, ..., 350
Power stability (rms, over 4 hours)	<1%, <2%, <3%	<2%, <3%, <5%
Transverse mode	TEM ₀₀	
M ² factor	<1.5	
Beam diameter at the aperture (1/e ² , mm)	0.70±0.05	
Beam divergence (mrad)	<1.5	
Polarization Ratio	>100:1, Vertical±5 degree	
Warm-up time (minutes)	<10	
Pointing stability after warm-up (mrad)	<0.05	
Beam height from base plate (mm)	27.4	
Laser head consumption(W)	15 (typical) , <25 (40℃)	
Max. Laser Head Base plate Temp (°C)	50	
Operating Temperature (°C)	10-40	
Power supply (90-264VAC)	PSU-H-LED/ PSU-H-FDA	
Expected lifetime (hours)	10000	
Warranty	1 year	



Note: The laser head needs to be used on a heat sink with good heat dissipation.

MBL-U-457	PSU-H-LED	PSU-H-FDA
<p>142.5 (L) × 60(W) × 50(H) mm³, 1.0 kg</p>	<p>277 (L) × 145(W) × 106 (H) mm³, 2.6 kg</p>	<p>236(L) × 145(W) × 104(H) mm³, 2.3 kg</p>



长春新产业光电技术有限公司

Changchun New Industries Optoelectronics Tech. Co., Ltd.

DATA SHEET