



MBL-U-xxx-OEM series



DPSS LASER

All solid state laser is made features of ultra compact, long lifetime, high stability and reliability, which is used in scientific experiment, medical measurement, instrument, spectrum analysis, etc.




SPECIFICATIONS

Part number	MBL-U-457-OEM		MBL-U-473-OEM	
Wavelength (nm)	457±1		473±1	
Operating mode	CW			
Output power (mW)	1-200	200-500	50-200	200-300
Power stability (rms, over 4 hours)	<3%,<2%,<1%	<3%,<2%,<1%	<3%,<2%,<1%	<3%,<2%,<1%
Transverse mode	TEM ₀₀			
M ² factor	<1.5		<1.2	
Beam diameter at the aperture (1/e ² , mm)	<1.0			
Beam divergence (mrad)	<1.5			
Polarization Ratio	>100:1, Vertical (Horizontal Optional)			
Warm-up time (minutes)	<5			
Pointing stability after warm-up (mrad)	<0.05			
Beam height from base plate (mm)	27.4			
Laser head consumption(W)	15 (typical) , <25 (40℃)			
Max. Laser Head Base plate Temp (°C)	50			
Operating Temperature (°C)	10-35			
Modulation optional	TTL on/off, 1Hz-1kHz, 1kHz-10kHz, 10kHz-30kHz; and Analog modulation optional			
Power supply (90-264VAC)	PSU-H-OEM/ PSU-SR-DC12V (OEM)/ PSU-SR-OEM			
Expected lifetime (hours)	10000			
Warranty	1 year			

Note: The laser head needs to be used on a heat sink with good heat dissipation.




LASER HEAD




142.5 (L) × 60 (W) × 50 (H) mm³, 1.0 kg

POWER SUPPLY (PSU-H-OEM)




235 (L) × 110 (W) × 45 (H) mm³, 1.1 kg

POWER SUPPLY (PSU-SR-DC12V)



152 (L) × 114 (W) × 50 (H) mm³, 0.5 kg

POWER SUPPLY (PSU-SR-OEM)



150 (L) × 111 (W) × 41.5 (H) mm³, 0.8 kg