



MBL-W-473A/1.5~2W




LD PUMPED ALL-SOLID-STATE
BLUE LASER

All solid state 473nm blue laser is made features of ultra compact, long lifetime and easy operating, which is used in fluorescence sensors, Raman spectrum, laser printing, holography, laser display, submarine communication, biomedicine, laser lighting show, etc.



SPECIFICATIONS

Wavelength (nm)	473±1	
Operating mode	CW	
Output power (W)	>1.5, 1.6, ..., 2	
Power stability (rms, over 4 hours)	<5%, <3%	
Transverse mode	TEM ₀₀	
M ² factor	<1.3	
Beam divergence, full angle (mrad)	<1.0	
Beam diameter at the aperture (1/e ² , mm)	~3.0	
Warm-up time (minutes)	<10	
Polarization ratio	>100:1	
Beam height from base plate (mm)	80	
Operating temperature (°C)	20~30	
Power supply (90-264VAC)	PSU-W-LED	PSU-W-FDA
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional	
Expected lifetime (hours)	10000	
Warranty period	1 year	



MBL-W-473A	PSU-W-LED	PSU-W-FDA
305 (L) × 120 (W) × 103 (H) mm³, 5.4 kg	342.1 (L) × 168 (W) × 143.4 (H) mm³, 4.2 kg	329.1 (L) × 168 (W) × 123 (H) mm³, 4.1 kg