

MDL-H-1064/1500~2500mW


## INFRARED DIODE LASER AT 1064nm





Diode infrared laser module at 1064nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in measurement, communication, spectrum analysis, etc.



### SPECIFICATIONS

Wavelength (nm)	1064±20		
Output power (mW)	>1500, 1600, ..., 2500		
Transverse mode	Multimode		
Operating mode	CW		
Power stability (rms, over 4 hours)	<1%, <3%, <5%		
Warm-up time (minutes)	<5		
M <sup>2</sup> factor	<20		
Beam divergence, full angle (mrad)	<3.0		
Beam diameter at the aperture (mm)	~5×8		
Beam height from base plate (mm)	29		
Operating temperature (°C)	10~35		
Power supply (90-264VAC)	PSU-H-LED	PSU-H-FDA	PSU-H-OEM
Modulation option	TTL/Analog 1Hz-5KHz, 1Hz-10KHz, 1Hz-30KHz, and TTL on/off		
Expected lifetime (hours)	10000		
Warranty period	1 year		



MxL-H-1064	PSU-H-LED	PSU-H-FDA	PSU-H-OEM
 <p>153(L)×77(W)×60(H) mm<sup>3</sup>, 0.9 kg</p>	 <p>268 (L) ×145(W) ×106 (H) mm<sup>3</sup>, 2.6 kg</p>	 <p>238 (L) ×146(W) ×102 (H) mm<sup>3</sup>, 2.3 kg</p>	 <p>238 (L) ×146(W) ×94 (H) mm<sup>3</sup>, 2.2 kg</p>
