



**MDL-III-937L/1~200mW**



**INFRARED DIODE LASER  
AT 937nm**

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are used in measurement, communication, spectrum analysis, etc.



**SPECIFICATIONS**

Central wavelength (nm)	937±3	
Operating mode	CW	
Output power (mW)	>1, 10, 20, ..., 200	
Power stability (rms, over 4 hours)	<3%, <2%, <1%, <0.5%	
Transverse mode	Near TEM <sub>00</sub>	
M <sup>2</sup> factor	~1.5 (~1.2, optional)	
Beam diameter at the aperture ((1/e <sup>2</sup> ),mm)	~3.5 (~1.2, optional)	
Beam divergence, full angle (mrad)	<1.0	
Warm-up time (minutes)	<5	
Pointing stability after warm-up (mrad)	<0.05	
Beam height from base plate (mm)	24.8	
Operating temperature (°C)	10~35	
Power supply	85-264VAC	PSU-III-LED/ PSU-III-FDA (Frequency for 1Hz-30kHz)
	100-240VAC	PSU-A-D (Frequency for 30kHz -100kHz)
Modulation optional	TTL on/off, 1Hz-1kHz, 1kHz-10kHz, 10kHz-30kHz, 30kHz-100kHz; and Analog modulation optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



MDL-III-937L	PSU-III-LED	PSU-III-FDA	PSU-A-D
<p style="text-align: center;">143.5(L)×73(W)×46.2(H) mm<sup>3</sup>, 0.7kg</p>	<p style="text-align: center;">188.6(L)×155(W)×92(H) mm<sup>3</sup>, 1.5kg</p>	<p style="text-align: center;">171(L)×130(W)×62.2(H) mm<sup>3</sup>, 1.2kg</p>	<p style="text-align: center;">162(L)×144(W)×70(H) mm<sup>3</sup>, 1.0kg</p>