



MDL-III-940R/1~400mW

**INFRARED DIODE LASER
AT 940nm**





Diode infrared laser module at 940 nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	940±5		
Output power (mW)	>1, 100, 200, 300, ..., 400		
Energy distribution	Even		
Beam Spot	Round		
Power stability (rms, over 4 hours)	<1%, <3%, <5%		
Warm-up time (minutes)	<5		
Beam divergence, full angle (mrad)	<8. 0		
Dimensions of beam at the aperture (mm)	~2.0		
Beam height from base plate (mm)	24. 8		
Pointing stability after warm-up (mrad)	<0.05		
Operating temperature (°C)	10~35		
Power supply (90-264VAC or 5VDC)	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
Modulation option	TTL/Analog 1Hz-5KHz, 1Hz-10KHz, 1Hz-30KHz, and TTL on/off		
Expected lifetime (hours)	10000		
Warranty	1 year		



MxL-III-940R	PSU-III-LED	PSU-III-FDA	PSU-III-OEM
 140. 8(L)×73(W) ×46. 2(H) mm ³ , 0.6kg	 154 (L) ×155(W) ×95 (H) mm ³ , 1.5kg	 133 (L) ×130(W) ×65 (H) mm ³ , 1.2kg	 100 (L) ×60(W) ×56 (H) mm ³ , 0.2kg
