



MDL-MD-650/655-OEM/1-1800mW




OEM RED DIODE LASER  
AT 650/655nm

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in measurement, spectrum analysis, laser lighting show, etc.



SPECIFICATIONS

Central wavelength (nm)	650±10/ 655±10
Operating mode	CW
Output power (mW)	>1, 100, 1000, ...,1800
Power stability (rms, over 4 hours)	<1%, <2%, <3%
Polarization direction	Horizontal + Vertical
Beam diameter at the aperture (mm)	~2×7
Beam divergence, full angle (mrad)	<4.7×4.0
Warm-up time (minutes)	<5
Beam height from base plate (mm)	28.5
Operating temperature (°C)	25+/-3
Driver (8VDC 7A)	PSU-SD-OEM
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty	1 year



MDL-MD-650/655-OEM	PSU-SD-OEM	Accessory (Power supply 100-240VAC)
<p>116(L)×75(W) ×54(H) mm<sup>3</sup>, 1.2kg</p>	<p>90.5 (L) ×47(W) ×56(H) mm<sup>3</sup>, 0.3kg</p>	<p>120 (L) ×60(W) ×37(H) mm<sup>3</sup>, 0.3kg</p>