

MDL-N-1530/1000~3500mW

INFRARED DIODE LASER AT 1530nm

Diode infrared laser module at 1530nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	1530±10	
Output power (mW)	>1000, 1500, 2000, ... , 3500	
Transverse mode	Near TE ₀₀	
Operating mode	CW	
Power stability (rms, over 4 hours)	<1%, <3%, <5%	
Warm-up time (minutes)	<5	
M ² factor	<20	
Beam divergence, full angle (mrad)	<3.0	
Beam diameter at the aperture (mm)	5~8	
Beam height from base plate (mm)	68.2	
Pointing stability after warm-up (mrad)	<0.05	
Operating temperature (°C)	10~35	
Power supply (90-264VAC)	PSU-H-LED	PSU-H-FDA
Modulation option	TTL/Analog 1Hz-5KHz, 1Hz-10KHz, 1Hz-30KHz, and TTL on/off	
Expected lifetime (hours)	10000	
Warranty period	1 year	



MDL-N-1530	PSU-H-LED	PSU-H-FDA
<p>240(L)×99(W)×94(H) mm³, 2.6 kg</p>	<p>268 (L) ×145(W) ×106 (H) mm³, 2.6 kg</p>	<p>238 (L) ×146(W) ×102 (H) mm³, 2.3 kg</p>