

MGL-DA-532/20~25W



LD PUMPED ALL-SOLID-STATE GREEN LASER

All solid state 532nm green laser is made features of ultra compact, long lifetime and easy operating, which is widely used in collimation, laser medical treatment, scientific experiment, optical instrument, laser display, laser lighting show, etc.



SPECIFICATIONS

Wavelength (nm)	532±1	
Operating mode	CW	
Output power (W)	>20, 21, ..., 24	>25
Power stability (rms, over 4 hours)	<5%, <3%, <2%, <1%	
Transverse mode	TEM ₀₀	
M ² factor	<1.3	<2
Beam divergence, full angle (mrad)	<1.5	
Beam diameter at the aperture (1/e ² , mm)	~1.5	
Cooled method	Water Cooled	
Warm-up time (minutes)	<10	
Beam height from base plate (mm)	90	
Operating temperature (°C)	10~35	
Power supply	100-240VAC	
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional	
Expected lifetime (hours)	10000	
Warranty period	1 year	



MGL-DA-532	Accessory (Power supply 100-240VAC)	Water Chiller (WCH-580)
<p>630 (L) × 222 (W) × 128 (H) mm³, 23.5 kg</p>	<p>220.6 (L) × 150 (W) × 112.5 (H) mm³, 2.8 kg</p>	<p>363.8 (L) × 253.2 (W) × 240.6 (H) mm³, 10.5 kg</p>