

长春新产业光电技术有限公司

Changehun New Industries Optoelectronics Tech. Co., Ltd.

DATA SHEET

MGL-F-540/1~500mW



LD PUMPED ALL-SOLID-STATE GREEN LASER

All solid state 540 nm green laser is made features of ultra compact, long lifetime, cost -effectiveness and easy operating, which is widely used in scientific experiment, laser fluorescence, treatment of facial capillary dilation, etc.









SPECIFICATIONS

Central wavelength (nm)	540±1	
Operating mode	CW	
Output power (mW)	>1, 5, 10, 20,, 200	>200,, 500
Power stability (rms, over 4 hours)	<3%, <5%	<3%, <5%, <10%
Transverse mode	Near TEM ₀₀	
M ² factor	<2.0	
Beam diameter at the aperture 1/e ² (mm)	~3. 0	
Beam divergence, full angle (mrad)	<2. 0	
Polarization ratio	>100:1	
Warm-up time (minutes)	<10	
Pointing stability after warm-up (mrad)	<0.05	
Beam height from base plate (mm)	45	
Operating temperature (°C)	10~35	
Power supply (90-264VAC)	PSU-H-LED/PSU-H-FDA/PSU-SR	
Expected lifetime (hours)	10000	
Warranty period	1 year	





