



MGL-FN-526.5/1~400mW



LD PUMPED ALL-SOLID-STATE GREEN LASER AT 526.5nm

All solid state 526.5nm green laser is made features of high output power stability, good beam profile, ultra compact, long lifetime, cost-effectiveness and easy operating, which is widely used in collimation, laser medical treatment, scientific experiment, optical instrument, etc.



SPECIFICATIONS

Central wavelength (nm)	526.5±1	
Operating mode	CW	
Output power (mW)	>1, 10, 50, ..., 200	>200, ..., 400
Power stability (rms, over 4 hours)	<2%, <3%, <5%	<3%, <5%
Transverse mode	Near TEM ₀₀	
M ² factor	<1.5	
Beam diameter at the aperture (1/e ² , mm)	~2.0	
Beam divergence, full angle (mrad)	<1.5	
Polarization ratio	>100:1 Horizontal±5 degree (Vertical Optional)	
Warm-up time (minutes)	<10	
Pointing stability after warm-up (mrad)	<0.05	
Beam height from base plate (mm)	27.4	
Operating temperature (°C)	10~35	
Power supply (90-264VAC)	PSU-H-LED/PSU-H-FDA/PSU-SR	
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option	
Expected lifetime (hours)	10000	
Warranty	1 year	



Note: The laser head needs to be used on a heat sink with good heat dissipation.

MGL-FN-526.5	PSU-H-LED	PSU-H-FDA	PSU-SR
<p>197(L)×70(W)×50(H) mm³, 1.5kg</p>	<p>277 (L) ×145(W) ×106 (H) mm³, 2.6 kg</p>	<p>275(L) ×145(W) ×104(H) mm³, 2.3 kg</p>	<p>188(L) ×145(W) ×83(H) mm³, 1.2kg</p>