



MGL-III-523.5/1~100mW



LD PUMPED ALL-SOLID-STATE GREEN LASER AT 523.5nm

All solid state laser at 523.5nm is made features of ultra compact, long lifetime, cost-effectiveness and easy operating, which is used in scientific experiment, optical sensor, measurement, instrument, communication, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	523.5±1		
Operating mode	CW		
Output power (mW)	>1, 5, 10, 20, ... , 100		
Power stability (rms, over 4 hours)	<2%, <3%, <5%		
Transverse mode	Near TEM <sub>00</sub>		
M <sup>2</sup> factor	<1.2		
Beam diameter at the aperture 1/e <sup>2</sup> (mm)	~1.2		
Beam divergence, full angle (mrad)	<1.5		
Polarization ratio	>100:1, Horizontal±5 degree (Vertical Optional)		
Warm-up time (minutes)	<10		
Pointing stability after warm-up (mrad)	<0.05		
Beam height from base plate (mm)	24.8		
Operating temperature (°C)	10~35		
Power supply (90-264VAC or 5VDC)	PSU-III-LED	PSU-III-FDA	PSU-III-OEM-97
Expected lifetime (hours)	10000		
Warranty	1 year		



MGL-III-523.5	PSU-III-LED	PSU-III-FDA	PSU-III-OEM-97
<p>140.5 (L) × 73 (W) × 46.2 (H) mm<sup>3</sup>, 0.6kg</p>	<p>153 (L) × 155 (W) × 92 (H) mm<sup>3</sup>, 1.5kg</p>	<p>133 (L) × 130 (W) × 62.2 (H) mm<sup>3</sup>, 1.2kg</p>	<p>94(L) × 75(W) × 49(H) mm<sup>3</sup>, 0.23kg</p>