



MGL-III-526.5/1~50mW



LD PUMPED ALL-SOLID-STATE
GREEN LASER AT 526.5nm

All solid state laser at 526.5nm is made features of ultra compact, long lifetime, cost-effectiveness and easy operating, which is used in scientific experiment, optical sensor, measurement, instrument, communication, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	526.5±1
Operating mode	CW
Output power (mW)	>1, 5, 10, 20, ... , 50
Power stability (rms, over 4 hours)	<2%, <3%, <5%
Transverse mode	Near TEM ₀₀
M ² factor	<1.2
Beam diameter at the aperture 1/e ² (mm)	~1.2
Beam divergence, full angle (mrad)	<1.5
Polarization ratio	>100:1, Horizontal ±5 degree (Vertical Optional)
Warm-up time (minutes)	<10
Pointing stability after warm-up (mrad)	<0.05
Beam height from base plate (mm)	24.8
Operating temperature (°C)	10~35
Power supply (90-264VAC or 5VDC)	PSU-III-LED PSU-III-FDA PSU-III-OEM-97
Expected lifetime (hours)	10000
Warranty	1 year



MGL-III-526.5	PSU-III-LED	PSU-III-FDA	PSU-III-OEM-97
<p>140.5 (L) × 73 (W) × 46.2 (H) mm³, 0.6kg</p>	<p>153 (L) × 155(W) × 92 (H) mm³, 1.5kg</p>	<p>133 (L) × 130(W) × 62.2 (H) mm³, 1.2kg</p>	<p>94(L) × 75(W) × 49(H) mm³, 0.23kg</p>