



MGL-III-532/200~400mW


LD PUMPED ALL-SOLID-STATE GREEN LASER

All solid state 532nm green laser is made features of high output power stability, good beam profile, ultra compact, long lifetime and easy operating, which is widely used in collimation, laser medical treatment, scientific experiment, optical instrument, laser display, laser lighting show, etc.



SPECIFICATIONS

Wavelength (nm)	532±1
Output power (mW)	>200, ..., 400
Transverse mode	TEM ₀₀
Operating mode	CW
Power stability (rms, over 4 hours)	<5%, <10%
Warm-up time (minutes)	<5
Beam divergence, full angle (mrad)	<1.5
Beam diameter at 1/e ² (mm)	~2
Beam height from base plate (mm)	24.8
Operating temperature (°C)	10~35
Power supply (100-240VAC or 5VDC)	PSU-III-OEM
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option
Expected lifetime (hours)	10000
Warranty	1 year



MGL-III-532	PSU-III-OEM	Adapter	Adapter
<p>140.8(L)×73(W)×46.2(H) mm³, 0.6kg</p>	<p>100 (L) ×62(W) ×56 (H) mm³, 0.2kg</p>	<p>85.2 (L) ×57.8(W) ×24.6 (H) mm³, 0.2kg</p>	<p>120(L)×60(W)×37(H) mm³, 0.1kg</p>