



MGL-U-588/50-200mW



DPSS LASER AT 588nm

All solid state laser at 588nm is made features of ultra compact, long lifetime, high stability and reliability, which is used in scientific experiment, medical measurement, instrument, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	588±1	
Operating mode	CW	
Output power (mW)	>50, ... , 100	>100, ... , 200
Power stability (rms, over 4 hours)	<1%, <2%, <3%	<2%, <3%, <5%
Transverse mode	TEM <sub>00</sub>	
M <sup>2</sup> factor	<1.2	
Beam diameter at the aperture (1/e <sup>2</sup> , mm)	<1.0	
Beam divergence (mrad)	<1.5	
Polarization Ratio	>100:1, Horizontal±5 degree	
Warm-up time (minutes)	<10	
Pointing stability after warm-up (mrad)	<0.05	
Beam height from base plate (mm)	27.4	
Laser head consumption(W)	15 (typical) , <25 (40°C)	
Max. Laser Head Base plate Temp (°C)	50	
Operating Temperature (°C)	10-40	
Driver (12VDC)	PSU-H-LED/PSU-H-FDA/PSU-SR	
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



Note: The laser head needs to be used on a heat sink with good heat dissipation.

MGL-U-588	PSU-H-LED	PSU-H-FDA	PSU-SR
<p>142.5 (L)×60(W) ×50(H) mm<sup>3</sup>, 1.0 kg</p>	<p>277 (L) ×145(W) ×106 (H) mm<sup>3</sup>, 2.6 kg</p>	<p>275(L) ×145(W) ×104(H) mm<sup>3</sup>, 2.3 kg</p>	<p>188(L) ×145(W) ×83(H) mm<sup>3</sup>, 1.2kg</p>