

长春新产业光电技术有限公司

Changehun New Industries Optoelectronics Tech. Co., Ltd.

DATA SHEET

MGL-W-532A/10~20W



LD PUMPED ALL-SOLID-STATE GREEN LASER

All solid state 532nm green laser is made features of ultra compact, long lifetime and easy operating, which is widely used in collimation, laser medical treatment, scientific experiment, optical instrument, laser display, laser lighting show, etc.









SPECIFICATIONS

Model	MGL-W-532A
Wavelength (nm)	532±1
Operating mode	CW
Output power (W)	>10, 11, 12,, 20
Power stability (rms, over 4 hours)	<5%, <3%, <1%
Transverse mode	Near TEM ₀₀
M ² factor	3~6
Beam divergence, full angle (mrad)	<2.0
Beam diameter at the aperture (1/e², mm)	~4.0
Warm-up time (minutes)	<10
Polarization ratio	>50:1(>100:1 optional), Horizontal(Vertical Optional)
Beam height from base plate (mm)	80
Operating temperature (°C)	10~35
Power supply (100-240VAC)	PSU-W-LED/PSU-W-FDA
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty period	1 year
Options	Linear power regulation 0-100% with constant beam quality. Part number: MGL-W-532A-HQ.





