

MIL-H-1047/500~1000mW



LD PUMPED ALL-SOLID-STATE INFRARED LASER AT 1047 nm




All solid state infrared laser at 1047nm is made features of ultra compact, long lifetime, cost -effectiveness and easy operating, which is used in scientific experiment, optical instrument, optical sensor, measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	1047±1
Operating mode	CW
Output power (mW)	>500, 550, 600, ... ,1000
Power stability (rms, over 4 hours)	<3%, <5%
Transverse mode	Near TEM ₀₀
M ² factor	<2. 0
Beam diameter at the aperture 1/e ² (mm)	~3. 0
Beam divergence, full angle (mrad)	<2. 0
Polarization ratio	>100:1 Horizontal±5 degree (Vertical Optional)
Warm-up time (minutes)	<10
Pointing stability after warm-up (mrad)	<0.05
Beam height from base plate (mm)	29
Operating temperature (°C)	10~35
Power supply (90-264VAC)	PSU-H-LED/PSU-H-FDA
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option
Expected lifetime (hours)	10000
Warranty period	1 year



MIL-H-1047	PSU-H-LED	PSU-H-FDA
 154.5(L)×77(W)×60(H) mm³, 0.9 kg	 277 (L) ×145(W) ×106 (H) mm³, 2.6 kg	 275(L) ×145(W) ×104(H) mm³, 2.3 kg