



MIL-III-1053/1~500mW




**LD PUMPED ALL-SOLID-STATE
INFRARED LASER AT 1053 nm**

All solid state infrared laser at 1053 nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in scientific experiment, measurement, optical instrument, optical sensor, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	1053±1
Operating mode	CW
Output power (mW)	>1, 5, 10, 20, ... , 500
Power stability (rms, over 4 hours)	<3%, <5%, <10%
Transverse mode	TEM ₀₀
M ² factor	<1.5
Beam diameter at the aperture 1/e ² (mm)	~1.5
Beam divergence, full angle (mrad)	<1.5
Polarization ratio	>100:1, Horizontal±5 degree (Vertical Optional)
Warm-up time (minutes)	<10
Pointing stability after warm-up (mrad)	<0.05
Beam height from base plate (mm)	24.8
Operating temperature (°C)	10~35
Power supply (90-264VAC or 5VDC)	PSU-III-LED/PSU-III-FDA/PSU-III-OEM-97
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option
Expected lifetime (hours)	10000
Warranty	1 year



MxL-III-1053	PSU-III-LED	PSU-III-FDA	PSU-III-OEM-97
<p>140.5 (L) × 73 (W) × 46.2 (H) mm³, 0.6kg</p>	<p>188 (L) × 155(W) × 92 (H) mm³, 1.5kg</p>	<p>171 (L) × 130(W) × 62.2 (H) mm³, 1.2kg</p>	<p>94(L) × 75(W) × 49(H) mm³, 0.23kg</p>