



MIL-III-1064/1~1500mW

LD PUMPED ALL-SOLID-STATE INFRARED LASER AT 1064 nm

All solid state infrared laser at 1064 nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in scientific experiment, measurement, optical instrument, optical sensor, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	1064±1	
Operating mode	CW	
Output power (mW)	>1, 5, 10, 20, ... , 1000	>1000, ... , 1500
Power stability (rms, over 4 hours)	<1%, <2%, <3%	<2%, <3%
Transverse mode	TEM ₀₀	
Warm-up time (minutes)	<10	
M ² factor	<1.5 (<1.2 optional)	<1.5
Beam divergence, full angle (mrad)	<1.5	
Beam diameter at 1/e ² (mm)	~1.5	
Beam height from base plate (mm)	24.8	
Polarization ratio	>100:1 Horizontal±5 degree (Vertical Optional)	
Pointing stability after warm-up (mrad)	<0.05	
Operating temperature (°C)	10~35	
Power supply (90-264VAC or 5VDC)	PSU-III-LED/PSU-III-FDA/PSU-III-OEM-97	
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option	
Expected lifetime (hours)	10000	
Warranty	1 year	



MIL-III-1064	PSU-III-LED	PSU-III-FDA	PSU-III-OEM-97
<p>140.5 (L) × 73 (W) × 46.2 (H) mm³, 0.6kg</p>	<p>188 (L) × 155(W) × 92 (H) mm³, 1.5kg</p>	<p>171 (L) × 130(W) × 62.2 (H) mm³, 1.2kg</p>	<p>94(L) × 75(W) × 49(H) mm³, 0.23kg</p>