



MIL-III-1313/1~400mW




**LD PUMPED ALL-SOLID-STATE
INFRARED LASER AT 1313 nm**

All solid state infrared laser at 1313 nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in scientific experiment, measurement, optical instrument, optical sensor, communication, spectrum analysis, etc.



SPECIFICATIONS

Wavelength (nm)	1313 ± 1	
Output power (mW)	>1, 5, 10, 20, ... , 200	>200, ... , 400
Power stability (rms, over 4 hours)	<1%, <2%, <3%, <5%	<2%, <3%, <5%
Transverse mode	TEM ₀₀	
Operating mode	CW	
Warm-up time (minutes)	<10	
M ² factor	<1.2	
Beam divergence, full angle (mrad)	<1.5	
Beam diameter at 1/e ² (mm)	~1.5	
Beam height from base plate (mm)	24.8	
Pointing stability after warm-up (mrad)	<0.05	
Operating temperature (°C)	10~35	
Power supply (90-264VAC or 5VDC)	PSU-III-LED/PSU-III-FDA/PSU-III-OEM-97	
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option	
Expected lifetime (hours)	10000	
Warranty	1 year	



MIL-III-1313	PSU-III-LED	PSU-III-FDA	PSU-III-OEM-97
<p style="text-align: center;">140.5 (L) × 73 (W) × 46.2 (H) mm³, 0.6kg</p>	<p style="text-align: center;">188 (L) × 155(W) × 92 (H) mm³, 1.5kg</p>	<p style="text-align: center;">171 (L) × 130(W) × 62.2 (H) mm³, 1.2kg</p>	<p style="text-align: center;">94(L) × 75(W) × 49(H) mm³, 0.23kg</p>