

MLL-H-1313/500~1000mW






**LOW NOISE INFRARED LASER
AT 1313 nm**

All solid state low noise infrared laser at 1313 nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in scientific experiment, optical instrument, optical sensor, measurement, communication, spectrum analysis, etc.

SPECIFICATIONS

Wavelength (nm)	1313 ± 1	
Output power (mW)	>500, 600, 700, ... ,800	>800, ... ,1000
Power stability (rms, over 4 hours)	<1%, <2%, <3%, <5%	<2%, <3%, <5%
Transverse mode	Near TEM ₀₀	
Operating mode	CW	
Noise of amplitude(rms, 20Hz~20MHz)	<1%	
Warm-up time (minutes)	<10	
M ² factor	<2. 0	
Beam divergence, full angle (mrad)	<2. 0	
Beam diameter at the aperture (mm)	~3. 0	
Beam height from base plate (mm)	29	
Polarization ratio	>100:1	
Pointing stability after warm-up (mrad)	<0.05	
Operating temperature (°C)	10~35	
Power supply (90-264VAC)	PSU-H-FDA/PSU-H-OEM	
Expected lifetime (hours)	10000	
Warranty period	1 year	



MLL-H-1313	PSU-H-FDA	PSU-H-OEM
 <p>154.5(L)×77(W)×60(H) mm³, 0.9 kg</p>	 <p>275(L)×145(W)×104(H) mm³, 2.3 kg</p>	 <p>245.5(L)×146(W)×94(H) mm³, 2.2 kg</p>